





- 1.0 GENERAL NOTES  
 1.1 ALL IMPERIAL DIMENSIONS ARE IN BRACKETS [X.XX]  
 1.2 MARK PART WITH IDENTIFICATION NUMBER
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS  
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING  
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005  
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER  
 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	JL1183 16MAR23	JAHAINES 40168212CMO



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;  
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM	PART NO.	DESCRIPTION	QTY.
1	V-CLAMP	CLAMP, 4 SLOT V	8
2	MT-381	5/8" X 12" GALV THREADED ROD	8
3	GWF05A	GALV FLAT WASHER HARDENED 5/8", 1.3OD	32
4	GWL-05	5/8" GALV LOCK WASHER	32
5	GN-05	5/8" GALV HEX NUT	32

DENSITY	94.07	lbs/in <sup>3</sup>
MASS	331.94	lbs
VOLUME	2976.3	in <sup>3</sup>
SURFACE AREA		in <sup>2</sup>
DENSITY	42759.18	g/mm <sup>3</sup>
MASS	5439920.05	grams
VOLUME	1920196.34	mm <sup>3</sup>
SURFACE AREA		mm <sup>2</sup>
HEIGHT	(311.2[12.3])	
LENGTH	212.7[8.4]	
WIDTH	304.8[12.0]	

**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE	X[.X] ± 6[0.25]	2 PLACE	.XX[.XXX] ± 1.50[0.06]
1 PLACE	.X[.XX] ± 3.0[0.12]	ANGLES	± 2°

FINISH: \_\_\_\_\_ MATERIAL: \_\_\_\_\_

REV.	NAME	DATE	TITLE
CE	JL1183	16MAR23	CLAMP, PIPE TO PIPE, 1.66" TO 4.50", HD
RW	JL1183	03/21/2023	
AD	YW1045	03/23/2023	
RE	YMENG	03/24/2023	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ANSI Y 14.5M-1994

SCALE: **1:2** DOCUMENT NO.: **MUK-MSK3D**

SIZE	Auth Group	INSL	MODEL	DRAWING			SHEET
<b>A2</b>				VERSION	STATUS	REVISION	1 OF 1
				00	RE	A	

ECN 40168212CMO