



Propel ULL Singlemode MPO-12 Distribution Module, 6 duplex LC/APC to 1X12f MPO/APC pinned, Method A Straight

- Ultra-low loss (ULL) with Method A polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Breakout module
Product Brand	Propel
Product Series	PPL

General Specifications

Functionality	Breakout
Color, front	Green
Color, rear	Black
Interface, front	LC/APC
Interface Feature, front	Internal shutters
Interface, rear	MPO
Interface Feature, rear	Internal shutters Key up/down MPO Pinned Standard
Polarity	Method A Pairs, straight
Total Fibers, quantity	12
Total Ports, quantity, front	6
Total Ports, quantity, rear	1

Dimensions

Height	11 mm 0.433 in
Width	98 mm 3.858 in
Depth	170 mm 6.693 in

Optical Specifications

760255928 | PPL-DM-12AP-12LA-SM-AS

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.65 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL UL 62368

Packaging and Weights

Packaging quantity	1
---------------------------	---