SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

For patents see www.cs-pat.com

Product Classification

Product TypeAdapterProduct BrandSnapStak®

Ordering Note CommScope® standard product in the United States and Canada

General Specifications

Color Black

Dimensions

 Height
 76.2 mm | 3 in

 Width
 25.4 mm | 1 in

 Length
 0.076 m | 0.25 ft

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Maximum Loading Quadruple stack for SSH-M | Triple stack for hangers SSH-XL, SSH-

L | Triple stack, 1-5/8 in cable

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

UV Resistance, minimum with no degradation ≥1000 hours

Packaging and Weights

 Height, packed
 17 cm | 6.693 in

 Width, packed
 13 cm | 5.118 in

 Length, packed
 10 cm | 3.937 in

COMMSCOPE®

SSHR-10

Packaging quantity 10

Weight, gross 0.15 kg | 0.331 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

