U4GQPLUTF

Base Product



Singlemode MPO8 APC non-pinned to LC/UPC Uniboot Ruggedized fanout Cable, 24-Fiber, LSZH, 8 fiber PmP 2.0 mm /B2ca

Product Classification

Regional Availability Europe

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity 3

Color, boot A Gray

Color, connector A Green

Connector B, quantity 24

Color, boot B Blue

Color, connector B Blue

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-08/APC Female

Interface, Connector B LC/UPC

Interface Feature, connector B Uniboot

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 24


Dimensions

COMMSCOPE®

U4GQPLUTF

Breakout Length22 inCable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 10



U4GQPLUTF

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted





Included Products

760254315 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 2.0 mm Subunits, N-024-MP-8G1-F08YL/20T/B2 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

860658160 – LC/UPC Uniboot Connector, Singlemode, Blue

860659028 – MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm



760254315 | N-024-MP-8G1-F08YL/20T/B2

24



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 2.0 mm Subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-free

Filler, quantity

Jacket ColorYellowJacket MarkingFeetSubunit, quantity3Fibers per Subunit, quantity8

Dimensions

Total Fiber Count

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket7.8 mm | 0.307 in

Mechanical Specifications

Minimum Bend Radius, loaded116 mm | 4.567 inMinimum Bend Radius, unloaded78 mm | 3.071 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

COMMSCOPE®

760254315 | N-024-MP-8G1-F08YL/20T/B2

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

 $\begin{tabular}{lll} \textbf{Vertical Rise, maximum} & 340 \ m & 1,115.486 \ ft \end{tabular}$

Optical Specifications

Fiber Type G.657.A2/B2

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} +60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +140 \, ^{\circ}\text{F})$ Operating Temperature $0 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3 | IEC 60754-2 | IEC 61034-2

Environmental Test Specifications

 Low High Bend
 0 °C to +70 °C (+32 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 60.1 kg/km | 40.385 lb/kft



760254315 | N-024-MP-8G1-F08YL/20T/B2

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LC/UPC Uniboot Connector, Singlemode, Blue

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

 Color, boot
 Blue

 Color, housing
 Blue

 Interface
 LC/UPC

Dimensions

Length 64 mm | 2.52 in

Compatible Cable Diameter 1.6 mm | 0.063 in | 2 mm | 0.079 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Singlemode

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568. 3-D | IEC 61753-1

Insertion Loss Change, temperature0.2 dBInsertion Loss, ULL, maximum0.25 dBReturn Loss, minimum55 dB

Regulatory Compliance/Certifications

COMMSC PE°

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)





MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Total Fiber Count 8

Dimensions

Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

COMMSCOPE®

Packaging quantity

1

Classification

Regulatory Compliance/Certifications

Agency CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant Compliant **UK-ROHS**

