

AVA5P-50FX-43B



AVA5-50FX, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 7/8 in, black PE jacket

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX®
Product Series	AVA5-50FX
Ordering Note	CommScope® non-standard product Not available in the United States or Canada

General Specifications

Flexibility	Standard
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric	24.13 mm 0.95 in
Diameter Over Jacket	27.991 mm 1.102 in
Inner Conductor OD	9.449 mm 0.372 in
Outer Conductor OD	25.4 mm 1 in
Nominal Size	7/8 in

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
Capacitance	73 pF/m 22.25 pF/ft
dc Resistance, Inner Conductor	2.888 ohms/km 0.88 ohms/kft
dc Resistance, Outer Conductor	1.53 ohms/km 0.466 ohms/kft
dc Test Voltage	6000 V
Inductance	0.184 µH/m 0.056 µH/ft
Insulation Resistance	100000 MOhms-km

AVA5P-50FX-43B

Jacket Spark Test Voltage (rms)	8000 V
Operating Frequency Band	1 – 5000 MHz
Peak Power	91 kW
Velocity	90 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
710–806 MHz	1.2	20.83
806–970 MHz	1.15	23.13
1420–1530 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13
2535–2655 MHz	1.2	20.83
3400–3800 MHz	1.253	18.99
3800–4200 MHz	1.253	18.99
4400–5000 MHz	1.4	15.56

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.113	0.034	74.43
1.5	0.138	0.042	60.73
2.0	0.16	0.049	52.56
10.0	0.359	0.11	23.37
20.0	0.51	0.156	16.46
30.0	0.627	0.191	13.39
50.0	0.814	0.248	10.32
85.0	1.068	0.326	7.86
88.0	1.088	0.332	7.72
100.0	1.162	0.354	7.23
108.0	1.209	0.368	6.95
150.0	1.433	0.437	5.86
174.0	1.548	0.472	5.43
200.0	1.665	0.507	5.05
204.0	1.682	0.513	4.99
300.0	2.059	0.628	4.08
400.0	2.398	0.731	3.5

AVA5P-50FX-43B

450.0	2.553	0.778	3.29
460.0	2.583	0.787	3.25
500.0	2.7	0.823	3.11
512.0	2.735	0.834	3.07
600.0	2.977	0.907	2.82
700.0	3.235	0.986	2.6
800.0	3.478	1.06	2.42
824.0	3.534	1.077	2.38
894.0	3.694	1.126	2.27
960.0	3.841	1.171	2.19
1000.0	3.927	1.197	2.14
1218.0	4.377	1.334	1.92
1250.0	4.44	1.353	1.89
1500.0	4.912	1.497	1.71
1700.0	5.268	1.605	1.59
1794.0	5.429	1.655	1.55
1800.0	5.439	1.658	1.54
2000.0	5.771	1.759	1.46
2100.0	5.933	1.808	1.42
2200.0	6.091	1.856	1.38
2300.0	6.247	1.904	1.34
2500.0	6.55	1.996	1.28
2700.0	6.845	2.086	1.23
3000.0	7.272	2.217	1.15
3400.0	7.819	2.383	1.07
3600.0	8.083	2.464	1.04
3700.0	8.213	2.503	1.02
3800.0	8.342	2.542	1.01
3900.0	8.47	2.581	0.99
4000.0	8.596	2.62	0.98
4100.0	8.722	2.658	0.96
4200.0	8.846	2.696	0.95
4300.0	8.969	2.734	0.94
4400.0	9.092	2.771	0.92
4500.0	9.213	2.808	0.91

AVA5P-50FX-43B

4600.0	9.333	2.845	0.9
4700.0	9.453	2.881	0.89
4800.0	9.572	2.917	0.88
4900.0	9.689	2.953	0.87
5000.0	9.806	2.989	0.86

Material Specifications

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Copper
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	254 mm 10 in
Minimum Bend Radius, single Bend	127 mm 5 in
Number of Bends, minimum	15
Number of Bends, typical	30
Tensile Strength	159 kg 350.535 lb
Bending Moment	19 N-m 168.164 in lb
Flat Plate Crush Strength	1.3 kg/mm 72.797 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +70 °C (-67 °F to +158 °F)
Storage Temperature	-70 °C to +70 °C (-94 °F to +158 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Cable weight	0.41 kg/m 0.276 lb/ft
---------------------	-------------------------