

Universal Open Pipe Mount Kit for straight or tapered legs

Product Classification

Product Type Pipe mount | Remote radio head unit mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

88.9 mm | 3.5 in

Pipe, quantity 1

Tower Taper Tapered

Dimensions

Pipe Outer Diameter

 Height
 1524 mm | 60 in

 Width
 457.2 mm | 18 in

 Length
 457.2 mm | 18 in

 Pipe Length
 1524 mm | 60 in

 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 0 mm | 0 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

COMMSCOPE®

RR-DPM

Included Brackets | Hardware | Pipe

Packaging quantity 1

Weight, net 109.2 kg | 240.745 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

