

PPLUGGRSNSNQ

Propel ULL Singlemode Cabled Module, 8x16 duplex SN Propel module on End A to 8x16 on End B, 128 fiber Plenum Trunk, Method B Enhanced

- This component requires 4 of the 12 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method B Enhanced polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cabled module
Product Brand	Propel
Product Series	PPL
Ordering Note	End B module is the same module as End A For lengths greater than 999 ft (304 m), orders must be in meters Maximum length is 400 meters

General Specifications

Configuration Type	PROPEL Module to PROPEL Module
Cable Color	Yellow
Cable Type	Trunk Cable - Plenum
Interface, front	SN/UPC
Interface Feature, front	Duplex Shuttered
Interface Color, front	Blue
Interface, rear	SN/UPC
Interface Feature, rear	Duplex Shuttered
Module Size, end A	8 fiber
Module Size, end B	8 fiber
Module Quantity, end A	8
Module Quantity, end B	8
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	128
Total Ports, quantity, front	64

PPLUGGRSNSNQ

Dimensions

Height	11 mm 0.433 in
Width	65 mm 2.559 in
Depth	170 mm 6.693 in
Breakout Length, end B	23 in
Cable Assembly Length Range (m)	1 – 400
Cable Assembly Length Range (ft)	2 – 999

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.6 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	c-UL-us

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

PPLUGGRSNSNQ

UK-ROHS

Compliant/Exempted



Included Products

- 760251019
P-128-MP-8G1-F16YL - Fiber indoor cable, Plenum MPO Trunk, 128 fiber multi-unit with 16 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color