

VSRA-MM-B3



Adjustable Monopole V-Stabilizer Kit 3- Sector with Ring mount - pipe not included

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Length 1,625.6 mm | 64 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 304.8 mm | 12 in

Stand-off Distance 1524 mm | 60 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Legs | Ring mount

Packaging quantity 1

Weight, net 65.771 kg | 145 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

VSRA-MM-B3



* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code