


MC-RMHD-1245-3

Universal Ring Mount, Heavy Duty 3-sector, 12 in to 45 in OD



Product Classification

Product Type Universal ring mount

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Sectors, quantity 3

Dimensions

Height 381 mm | 15 in

Mounting Diameter, maximum 1,143 mm | 45 in

Mounting Diameter, minimum 304.8 mm | 12 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Mount | Threaded rod

Packaging quantity 1

Weight, net 149.323 kg | 329.2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

MC-RMHD-1245-3

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

