

# F1A-TNRNR-M815-C4



FSJ1-50A SureFlex® Jumper with interface types N Male Right Angle and N Male Right Angle, 0.815 m

**OBSOLETE**

This product was discontinued on: January 29, 2008

## Product Classification

|                       |                     |
|-----------------------|---------------------|
| <b>Product Type</b>   | SureFlex® standard  |
| <b>Product Brand</b>  | HELIAX®   SureFlex® |
| <b>Product Series</b> | FSJ1-50A            |

## General Specifications

|   |             |
|---|-------------|
| <b>Body Style, Connector A</b>            | Right angle |
| <b>Body Style, Connector B</b>            | Right angle |
| <b>Interface, Connector A</b>             | N Male      |
| <b>Interface, Connector B</b>             | N Male      |
| <b>Orientation</b>                        | 0°          |
| <b>Specification Sheet Revision Level</b> | A           |

## Dimensions

|                     |                    |
|---------------------|--------------------|
| <b>Length</b>       | 0.815 m   2.674 ft |
| <b>Nominal Size</b> | 1/4 in             |

## Electrical Specifications

|                         |          |
|-------------------------|----------|
| <b>3rd Order IMD</b>    | -80 dBm  |
| <b>DTF, Connector A</b> | -29.5 dB |
| <b>DTF, Connector B</b> | -29.5 dB |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 400–2200 MHz   | 1.2  | 20.83            |

## Jumper Assembly Sample Label

# F1A-TNRNR-M815-C4



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015


### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- |            |   |  |
|------------|---|--|
| 35422-33   | - | Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket  |
| 35422-75   | - | Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket            |
| FSJ1-50A   | - | FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket   |
| FSJ1RK-50A | - | FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a d0 a1 Compliant |



Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket

## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Coaxial wireless cable |
| <b>Product Brand</b>  | HELIAX®                |
| <b>Product Series</b> | FSJ1-50A               |

## General Specifications

|                         |  |
|-------------------------|--|
| <b>Flexibility</b>      | Superflexible                                    |
| <b>Jacket Color</b>     | Black  |
| <b>Performance Note</b> | Attenuation values typical, guaranteed within 5% |

## Dimensions

|                                 |                     |
|---------------------------------|---------------------|
| <b>Diameter Over Dielectric</b> | 4.826 mm   0.19 in  |
| <b>Diameter Over Jacket</b>     | 7.366 mm   0.29 in  |
| <b>Inner Conductor OD</b>       | 1.905 mm   0.075 in |
| <b>Outer Conductor OD</b>       | 6.35 mm   0.25 in   |
| <b>Nominal Size</b>             | 1/4 in              |

## Electrical Specifications

|  |                            |
|--|----------------------------|
| <b>Cable Impedance</b>                 | 50 ohm ±1 ohm              |
| <b>Capacitance</b>                     | 79.4 pF/m   24.201 pF/ft   |
| <b>dc Resistance, Inner Conductor</b>  | 9.843 ohms/km   3 ohms/kft |
| <b>dc Resistance, Outer Conductor</b>  | 6.562 ohms/km   2 ohms/kft |
| <b>dc Test Voltage</b>                 | 1600 V                     |
| <b>Inductance</b>                      | 0.2 µH/m   0.061 µH/ft     |
| <b>Insulation Resistance</b>           | 100000 MOhms-km            |
| <b>Jacket Spark Test Voltage (rms)</b> | 5000 V                     |
| <b>Operating Frequency Band</b>        | 1 – 18000 MHz              |

# 35422-33

---

**Peak Power** 6.4 kW

**Velocity** 82 %

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 680–960 MHz    | 1.201 | 20.79            |
| 1700–2200 MHz  | 1.201 | 20.79            |
| 2200–2700 MHz  | 1.433 | 14.99            |

## Attenuation

| Frequency (MHz) | Attenuation (dB/100 m) | Attenuation (dB/100 ft) |
|-----------------|------------------------|-------------------------|
| 0.5             | 0.407                  | 0.124                   |
| 1.0             | 0.577                  | 0.176                   |
| 1.5             | 0.707                  | 0.215                   |
| 2.0             | 0.816                  | 0.249                   |
| 10.0            | 1.833                  | 0.559                   |
| 20.0            | 2.6                    | 0.792                   |
| 30.0            | 3.192                  | 0.973                   |
| 50.0            | 4.136                  | 1.261                   |
| 85.0            | 5.419                  | 1.652                   |
| 88.0            | 5.516                  | 1.681                   |
| 100.0           | 5.889                  | 1.795                   |
| 108.0           | 6.12                   | 1.867                   |
| 150.0           | 7.25                   | 2.21                    |
| 174.0           | 7.825                  | 2.385                   |
| 200.0           | 8.408                  | 2.563                   |
| 204.0           | 8.495                  | 2.589                   |
| 300.0           | 10.373                 | 3.162                   |
| 400.0           | 12.051                 | 3.673                   |
| 450.0           | 12.817                 | 3.906                   |
| 500.0           | 13.545                 | 4.128                   |
| 512.0           | 13.715                 | 4.18                    |
| 600.0           | 14.909                 | 4.544                   |
| 700.0           | 16.175                 | 4.93                    |
| 800.0           | 17.362                 | 5.292                   |

# 35422-33

---

|         |         |        |
|---------|---------|--------|
| 824.0   | 17.637  | 5.376  |
| 894.0   | 18.42   | 5.614  |
| 960.0   | 19.134  | 5.832  |
| 1000.0  | 19.556  | 5.96   |
| 1218.0  | 21.738  | 6.626  |
| 1250.0  | 22.044  | 6.719  |
| 1500.0  | 24.326  | 7.414  |
| 1700.0  | 26.038  | 7.936  |
| 1794.0  | 26.813  | 8.172  |
| 1800.0  | 26.862  | 8.187  |
| 2000.0  | 28.455  | 8.673  |
| 2100.0  | 29.227  | 8.908  |
| 2200.0  | 29.984  | 9.139  |
| 2300.0  | 30.727  | 9.365  |
| 2500.0  | 32.174  | 9.806  |
| 2700.0  | 33.576  | 10.233 |
| 3000.0  | 35.602  | 10.851 |
| 3400.0  | 38.183  | 11.638 |
| 3700.0  | 40.041  | 12.204 |
| 4000.0  | 41.841  | 12.753 |
| 5000.0  | 47.5    | 14.477 |
| 6000.0  | 52.747  | 16.077 |
| 8000.0  | 62.37   | 19.01  |
| 8800.0  | 65.974  | 20.108 |
| 10000.0 | 71.173  | 21.693 |
| 12000.0 | 79.393  | 24.198 |
| 14000.0 | 87.172  | 26.569 |
| 15800.0 | 93.872  | 28.611 |
| 16000.0 | 94.601  | 28.833 |
| 18000.0 | 101.745 | 31.01  |

## Material Specifications

|                                 |                           |
|---------------------------------|---------------------------|
| <b>Dielectric Material</b>      | Foam PE                   |
| <b>Jacket Material</b>          | PE                        |
| <b>Inner Conductor Material</b> | Copper-clad aluminum wire |

# 35422-33

---

**Outer Conductor Material** Corrugated copper

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 25.4 mm | 1 in  
**Minimum Bend Radius, single Bend** 25.4 mm | 1 in  
**Number of Bends, minimum** 15  
**Number of Bends, typical** 20  
**Tensile Strength** 68 kg | 149.914 lb  
**Bending Moment** 1.1 N-m | 9.736 in lb  
**Flat Plate Crush Strength** 1.8 kg/mm | 100.795 lb/in

## Environmental Specifications

**Installation temperature** -40 °C to +60 °C (-40 °F to +140 °F)  
**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)  
**Storage Temperature** -70 °C to +85 °C (-94 °F to +185 °F)  
**Attenuation, Ambient Temperature** 68 °F | 20 °C  
**Average Power, Ambient Temperature** 104 °F | 40 °C  
**Average Power, Inner Conductor Temperature** 212 °F | 100 °C

## Packaging and Weights

**Cable weight** 0.07 kg/m | 0.047 lb/ft

## Regulatory Compliance/Certifications

| Agency               | Classification   |
|----------------------|--|
| ISO 9001:2015        | Designed, manufactured and/or distributed under this quality management system |
| UL/ETL Certification | Compliant  |



# 35422-75

---



Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket

## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Coaxial wireless cable |
| <b>Product Brand</b>  | HELIAX®                |
| <b>Product Series</b> | FSJ1-50B               |

## General Specifications

|                         |  |
|-------------------------|--|
| <b>Flexibility</b>      | Superflexible                                    |
| <b>Jacket Color</b>     | Black  |
| <b>Performance Note</b> | Attenuation values typical, guaranteed within 5% |

## Dimensions

|                                 |                     |
|---------------------------------|---------------------|
| <b>Diameter Over Dielectric</b> | 4.826 mm   0.19 in  |
| <b>Diameter Over Jacket</b>     | 7.62 mm   0.3 in    |
| <b>Inner Conductor OD</b>       | 1.905 mm   0.075 in |
| <b>Outer Conductor OD</b>       | 6.35 mm   0.25 in   |
| <b>Nominal Size</b>             | 1/4 in              |

## Electrical Specifications

|  |                            |
|--|----------------------------|
| <b>Cable Impedance</b>                 | 50 ohm ±1 ohm              |
| <b>Capacitance</b>                     | 79.4 pF/m   24.201 pF/ft   |
| <b>dc Resistance, Inner Conductor</b>  | 9.843 ohms/km   3 ohms/kft |
| <b>dc Resistance, Outer Conductor</b>  | 6.562 ohms/km   2 ohms/kft |
| <b>dc Test Voltage</b>                 | 1600 V                     |
| <b>Inductance</b>                      | 0.2 µH/m   0.061 µH/ft     |
| <b>Insulation Resistance</b>           | 100000 MOhms-km            |
| <b>Jacket Spark Test Voltage (rms)</b> | 4000 V                     |
| <b>Operating Frequency Band</b>        | 1 – 18000 MHz              |

# 35422-75

|                   |        |
|-------------------|--------|
| <b>Peak Power</b> | 6.4 kW |
| <b>Velocity</b>   | 82 %   |

## VSWR/Return Loss

| <b>Frequency Band</b> | <b>VSWR</b> | <b>Return Loss (dB)</b> |
|-----------------------|-------------|-------------------------|
| <b>680–960 MHz</b>    | 1.201       | 20.79                   |
| <b>1700–2200 MHz</b>  | 1.201       | 20.79                   |
| <b>2200–2700 MHz</b>  | 1.433       | 14.99                   |

## Attenuation

| <b>Frequency (MHz)</b> | <b>Attenuation (dB/100 m)</b> | <b>Attenuation (dB/100 ft)</b> | <b>Average Power (kW)</b> |
|------------------------|-------------------------------|--------------------------------|---------------------------|
| <b>1.0</b>             | 0.577                         | 0.176                          | 6.4                       |
| <b>1.5</b>             | 0.707                         | 0.215                          | 6.4                       |
| <b>2.0</b>             | 0.816                         | 0.249                          | 6.4                       |
| <b>10.0</b>            | 1.833                         | 0.559                          | 3.99                      |
| <b>20.0</b>            | 2.6                           | 0.792                          | 2.81                      |
| <b>30.0</b>            | 3.192                         | 0.973                          | 2.29                      |
| <b>50.0</b>            | 4.136                         | 1.261                          | 1.77                      |
| <b>85.0</b>            | 5.419                         | 1.652                          | 1.35                      |
| <b>88.0</b>            | 5.516                         | 1.681                          | 1.33                      |
| <b>100.0</b>           | 5.889                         | 1.795                          | 1.24                      |
| <b>108.0</b>           | 6.125                         | 1.867                          | 1.19                      |
| <b>150.0</b>           | 7.25                          | 2.21                           | 1.01                      |
| <b>174.0</b>           | 7.825                         | 2.385                          | 0.93                      |
| <b>200.0</b>           | 8.408                         | 2.563                          | 0.87                      |
| <b>204.0</b>           | 8.495                         | 2.589                          | 0.86                      |
| <b>300.0</b>           | 10.373                        | 3.162                          | 0.71                      |
| <b>400.0</b>           | 12.051                        | 3.673                          | 0.61                      |
| <b>450.0</b>           | 12.817                        | 3.906                          | 0.57                      |
| <b>460.0</b>           | 12.965                        | 3.952                          | 0.56                      |
| <b>500.0</b>           | 13.545                        | 4.128                          | 0.54                      |
| <b>512.0</b>           | 13.715                        | 4.18                           | 0.53                      |
| <b>600.0</b>           | 14.909                        | 4.544                          | 0.49                      |
| <b>700.0</b>           | 16.175                        | 4.93                           | 0.45                      |
| <b>800.0</b>           | 17.362                        | 5.292                          | 0.42                      |



# 35422-75

---

|               |        |        |      |
|---------------|--------|--------|------|
| <b>824.0</b>  | 17.637 | 5.376  | 0.41 |
| <b>894.0</b>  | 18.42  | 5.614  | 0.4  |
| <b>960.0</b>  | 19.134 | 5.832  | 0.38 |
| <b>1000.0</b> | 19.556 | 5.96   | 0.37 |
| <b>1218.0</b> | 21.738 | 6.626  | 0.34 |
| <b>1250.0</b> | 22.044 | 6.719  | 0.33 |
| <b>1500.0</b> | 24.326 | 7.414  | 0.3  |
| <b>1700.0</b> | 26.038 | 7.936  | 0.28 |
| <b>1794.0</b> | 26.813 | 8.172  | 0.27 |
| <b>1800.0</b> | 26.862 | 8.187  | 0.27 |
| <b>2000.0</b> | 28.455 | 8.673  | 0.26 |
| <b>2100.0</b> | 29.227 | 8.908  | 0.25 |
| <b>2200.0</b> | 29.984 | 9.139  | 0.24 |
| <b>2300.0</b> | 30.727 | 9.365  | 0.24 |
| <b>2500.0</b> | 32.174 | 9.806  | 0.23 |
| <b>2700.0</b> | 33.576 | 10.233 | 0.22 |
| <b>3000.0</b> | 35.602 | 10.851 | 0.21 |
| <b>3400.0</b> | 38.183 | 11.638 | 0.19 |
| <b>3600.0</b> | 39.428 | 12.017 | 0.19 |
| <b>3700.0</b> | 40.041 | 12.204 | 0.18 |
| <b>3800.0</b> | 40.647 | 12.389 | 0.18 |
| <b>3900.0</b> | 41.247 | 12.571 | 0.18 |
| <b>4000.0</b> | 41.841 | 12.753 | 0.17 |
| <b>4100.0</b> | 42.429 | 12.932 | 0.17 |
| <b>4200.0</b> | 43.012 | 13.11  | 0.17 |
| <b>4300.0</b> | 43.59  | 13.286 | 0.17 |
| <b>4400.0</b> | 44.163 | 13.46  | 0.17 |
| <b>4500.0</b> | 44.73  | 13.633 | 0.16 |
| <b>4600.0</b> | 45.293 | 13.805 | 0.16 |
| <b>4700.0</b> | 45.852 | 13.975 | 0.16 |
| <b>4800.0</b> | 46.405 | 14.144 | 0.16 |
| <b>4900.0</b> | 46.955 | 14.311 | 0.16 |
| <b>5000.0</b> | 47.5   | 14.477 | 0.15 |
| <b>6000.0</b> | 52.747 | 16.077 | 0.14 |
| <b>8000.0</b> | 62.37  | 19.01  | 0.12 |

# 35422-75

---

|                |         |        |      |
|----------------|---------|--------|------|
| <b>8800.0</b>  | 65.974  | 20.108 | 0.11 |
| <b>10000.0</b> | 71.173  | 21.693 | 0.1  |
| <b>12000.0</b> | 79.393  | 24.198 | 0.09 |
| <b>14000.0</b> | 87.172  | 26.569 | 0.08 |
| <b>15800.0</b> | 93.872  | 28.611 | 0.08 |
| <b>16000.0</b> | 94.601  | 28.833 | 0.08 |
| <b>18000.0</b> | 101.745 | 31.01  | 0.07 |

## Material Specifications

|                                 |  |
|---------------------------------|--|
| <b>Dielectric Material</b>      | Foam PE                                    |
| <b>Jacket Material</b>          | Non-halogenated, fire retardant polyolefin |
| <b>Inner Conductor Material</b> | Copper-clad aluminum wire                  |
| <b>Outer Conductor Material</b> | Corrugated copper                          |

## Mechanical Specifications

|  |                           |
|--|---------------------------|
| <b>Minimum Bend Radius, multiple Bends</b> | 25.4 mm   1 in            |
| <b>Minimum Bend Radius, single Bend</b>    | 25.4 mm   1 in            |
| <b>Number of Bends, minimum</b>            | 15                        |
| <b>Number of Bends, typical</b>            | 20                        |
| <b>Tensile Strength</b>                    | 68 kg   149.914 lb        |
| <b>Bending Moment</b>                      | 1.1 N-m   9.736 in lb     |
| <b>Flat Plate Crush Strength</b>           | 1.8 kg/mm   100.795 lb/in |

## Environmental Specifications

|   |                                      |
|---|--------------------------------------|
| <b>Installation temperature</b>                   | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Operating Temperature</b>                      | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Storage Temperature</b>                        | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Attenuation, Ambient Temperature</b>           | 68 °F   20 °C                        |
| <b>Average Power, Ambient Temperature</b>         | 104 °F   40 °C                       |
| <b>Average Power, Inner Conductor Temperature</b> | 212 °F   100 °C                      |
| <b>Fire Retardancy Test Method</b>                | UL 1666/CATVR/CMR                    |
| <b>Smoke Index Test Method</b>                    | IEC 61034                            |
| <b>Toxicity Index Test Method</b>                 | IEC 60754-1   IEC 60754-2            |

# 35422-75

---

## Packaging and Weights

**Cable weight** 0.07 kg/m | 0.047 lb/ft

## Regulatory Compliance/Certifications

| Agency               | Classification   |
|----------------------|--|
| ISO 9001:2015        | Designed, manufactured and/or distributed under this quality management system |
| UL/ETL Certification | Compliant  |



# FSJ1-50A



FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Coaxial wireless cable |
| <b>Product Brand</b>  | HELIAX®   SureFlex®    |
| <b>Product Series</b> | FSJ1-50A   MLOC        |

## General Specifications

|                         |  |
|-------------------------|--|
| <b>Product Number</b>   | 887009902/00   SZ887009902/00                    |
| <b>Flexibility</b>      | Superflexible                                    |
| <b>Jacket Color</b>     | Black  |
| <b>Performance Note</b> | Attenuation values typical, guaranteed within 5% |

## Dimensions

|                                 |                     |
|---------------------------------|---------------------|
| <b>Diameter Over Dielectric</b> | 4.826 mm   0.19 in  |
| <b>Diameter Over Jacket</b>     | 7.366 mm   0.29 in  |
| <b>Inner Conductor OD</b>       | 1.905 mm   0.075 in |
| <b>Outer Conductor OD</b>       | 6.35 mm   0.25 in   |
| <b>Nominal Size</b>             | 1/4 in              |

## Electrical Specifications

|  |                                |
|--|--------------------------------|
| <b>Cable Impedance</b>                 | 50 ohm ±1 ohm                  |
| <b>Capacitance</b>                     | 79.4 pF/m   24.201 pF/ft       |
| <b>dc Resistance, Inner Conductor</b>  | 9.843 ohms/km   3 ohms/kft     |
| <b>dc Resistance, Outer Conductor</b>  | 7.216 ohms/km   2.199 ohms/kft |
| <b>dc Test Voltage</b>                 | 1600 V                         |
| <b>Inductance</b>                      | 0.2 µH/m   0.061 µH/ft         |
| <b>Insulation Resistance</b>           | 100000 MOhms-km                |
| <b>Jacket Spark Test Voltage (rms)</b> | 5000 V                         |

# FSJ1-50A

|                                 |               |
|---------------------------------|---------------|
| <b>Operating Frequency Band</b> | 1 – 18000 MHz |
| <b>Peak Power</b>               | 6.4 kW        |
| <b>Velocity</b>                 | 82 %          |

## VSWR/Return Loss

| <b>Frequency Band</b> | <b>VSWR</b> | <b>Return Loss (dB)</b> |
|-----------------------|-------------|-------------------------|
| <b>680–960 MHz</b>    | 1.201       | 20.8                    |
| <b>1700–2200 MHz</b>  | 1.201       | 20.8                    |
| <b>2200–2700 MHz</b>  | 1.433       | 15                      |

## Attenuation

| <b>Frequency (MHz)</b> | <b>Attenuation (dB/100 m)</b> | <b>Attenuation (dB/100 ft)</b> | <b>Average Power (kW)</b> |
|------------------------|-------------------------------|--------------------------------|---------------------------|
| <b>1.0</b>             | 0.577                         | 0.176                          | 6.4                       |
| <b>1.5</b>             | 0.707                         | 0.215                          | 6.4                       |
| <b>2.0</b>             | 0.816                         | 0.249                          | 6.4                       |
| <b>10.0</b>            | 1.833                         | 0.559                          | 3.99                      |
| <b>20.0</b>            | 2.6                           | 0.792                          | 2.81                      |
| <b>30.0</b>            | 3.192                         | 0.973                          | 2.29                      |
| <b>50.0</b>            | 4.136                         | 1.261                          | 1.77                      |
| <b>85.0</b>            | 5.419                         | 1.652                          | 1.35                      |
| <b>88.0</b>            | 5.516                         | 1.681                          | 1.33                      |
| <b>100.0</b>           | 5.889                         | 1.795                          | 1.24                      |
| <b>108.0</b>           | 6.125                         | 1.867                          | 1.19                      |
| <b>150.0</b>           | 7.25                          | 2.21                           | 1.01                      |
| <b>174.0</b>           | 7.825                         | 2.385                          | 0.93                      |
| <b>200.0</b>           | 8.408                         | 2.563                          | 0.87                      |
| <b>204.0</b>           | 8.495                         | 2.589                          | 0.86                      |
| <b>300.0</b>           | 10.373                        | 3.162                          | 0.71                      |
| <b>400.0</b>           | 12.051                        | 3.673                          | 0.61                      |
| <b>450.0</b>           | 12.817                        | 3.906                          | 0.57                      |
| <b>460.0</b>           | 12.965                        | 3.952                          | 0.56                      |
| <b>500.0</b>           | 13.545                        | 4.128                          | 0.54                      |
| <b>512.0</b>           | 13.715                        | 4.18                           | 0.53                      |
| <b>600.0</b>           | 14.909                        | 4.544                          | 0.49                      |
| <b>700.0</b>           | 16.175                        | 4.93                           | 0.45                      |

# FSJ1-50A

---

|               |        |        |      |
|---------------|--------|--------|------|
| <b>800.0</b>  | 17.362 | 5.292  | 0.42 |
| <b>824.0</b>  | 17.637 | 5.376  | 0.41 |
| <b>894.0</b>  | 18.42  | 5.614  | 0.4  |
| <b>960.0</b>  | 19.134 | 5.832  | 0.38 |
| <b>1000.0</b> | 19.556 | 5.96   | 0.37 |
| <b>1218.0</b> | 21.738 | 6.626  | 0.34 |
| <b>1250.0</b> | 22.044 | 6.719  | 0.33 |
| <b>1500.0</b> | 24.326 | 7.414  | 0.3  |
| <b>1700.0</b> | 26.038 | 7.936  | 0.28 |
| <b>1794.0</b> | 26.813 | 8.172  | 0.27 |
| <b>1800.0</b> | 26.862 | 8.187  | 0.27 |
| <b>2000.0</b> | 28.455 | 8.673  | 0.26 |
| <b>2100.0</b> | 29.227 | 8.908  | 0.25 |
| <b>2200.0</b> | 29.984 | 9.139  | 0.24 |
| <b>2300.0</b> | 30.727 | 9.365  | 0.24 |
| <b>2500.0</b> | 32.174 | 9.806  | 0.23 |
| <b>2700.0</b> | 33.576 | 10.233 | 0.22 |
| <b>3000.0</b> | 35.602 | 10.851 | 0.21 |
| <b>3400.0</b> | 38.183 | 11.638 | 0.19 |
| <b>3600.0</b> | 39.428 | 12.017 | 0.19 |
| <b>3700.0</b> | 40.041 | 12.204 | 0.18 |
| <b>3800.0</b> | 40.647 | 12.389 | 0.18 |
| <b>3900.0</b> | 41.247 | 12.571 | 0.18 |
| <b>4000.0</b> | 41.841 | 12.753 | 0.17 |
| <b>4100.0</b> | 42.429 | 12.932 | 0.17 |
| <b>4200.0</b> | 43.012 | 13.11  | 0.17 |
| <b>4300.0</b> | 43.59  | 13.286 | 0.17 |
| <b>4400.0</b> | 44.163 | 13.46  | 0.17 |
| <b>4500.0</b> | 44.73  | 13.633 | 0.16 |
| <b>4600.0</b> | 45.293 | 13.805 | 0.16 |
| <b>4700.0</b> | 45.852 | 13.975 | 0.16 |
| <b>4800.0</b> | 46.405 | 14.144 | 0.16 |
| <b>4900.0</b> | 46.955 | 14.311 | 0.16 |
| <b>5000.0</b> | 47.5   | 14.477 | 0.15 |
| <b>6000.0</b> | 52.747 | 16.077 | 0.14 |

# FSJ1-50A

---

|                |         |        |      |
|----------------|---------|--------|------|
| <b>8000.0</b>  | 62.37   | 19.01  | 0.12 |
| <b>8800.0</b>  | 65.974  | 20.108 | 0.11 |
| <b>10000.0</b> | 71.173  | 21.693 | 0.1  |
| <b>12000.0</b> | 79.393  | 24.198 | 0.09 |
| <b>14000.0</b> | 87.172  | 26.569 | 0.08 |
| <b>15800.0</b> | 93.872  | 28.611 | 0.08 |
| <b>16000.0</b> | 94.601  | 28.833 | 0.08 |
| <b>18000.0</b> | 101.745 | 31.01  | 0.07 |

## Material Specifications

|                                 |                           |
|---------------------------------|---------------------------|
| <b>Dielectric Material</b>      | Foam PE                   |
| <b>Jacket Material</b>          | PE                        |
| <b>Inner Conductor Material</b> | Copper-clad aluminum wire |
| <b>Outer Conductor Material</b> | Corrugated copper         |

## Mechanical Specifications

|  |                           |
|--|---------------------------|
| <b>Minimum Bend Radius, multiple Bends</b> | 25.4 mm   1 in            |
| <b>Minimum Bend Radius, single Bend</b>    | 25.4 mm   1 in            |
| <b>Number of Bends, minimum</b>            | 15                        |
| <b>Number of Bends, typical</b>            | 20                        |
| <b>Tensile Strength</b>                    | 68 kg   149.914 lb        |
| <b>Bending Moment</b>                      | 0.7 N-m   6.196 in lb     |
| <b>Flat Plate Crush Strength</b>           | 1.8 kg/mm   100.795 lb/in |

## Environmental Specifications

|   |                                      |
|---|--------------------------------------|
| <b>Installation temperature</b>                   | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Operating Temperature</b>                      | -55 °C to +85 °C (-67 °F to +185 °F) |
| <b>Storage Temperature</b>                        | -70 °C to +85 °C (-94 °F to +185 °F) |
| <b>Attenuation, Ambient Temperature</b>           | 68 °F   20 °C                        |
| <b>Average Power, Ambient Temperature</b>         | 104 °F   40 °C                       |
| <b>Average Power, Inner Conductor Temperature</b> | 212 °F   100 °C                      |

## Packaging and Weights

|                     |                         |
|---------------------|-------------------------|
| <b>Cable weight</b> | 0.07 kg/m   0.047 lb/ft |
|---------------------|-------------------------|

# FSJ1-50A

---

## Regulatory Compliance/Certifications

| <b>Agency</b>        | <b>Classification</b>  |
|----------------------|--|
| CHINA-ROHS           | Above maximum concentration value  |
| ISO 9001:2015        | Designed, manufactured and/or distributed under this quality management system |
| ROHS                 | Compliant  |
| UK-ROHS              | Compliant  |
| UL/ETL Certification | Compliant  |





# FSJ1RK-50A

---

FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a d0 a1 Compliant

## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Coaxial wireless cable |
| <b>Product Brand</b>  | HELIAX®   SureFlex®    |
| <b>Product Series</b> | FSJ1-50A   MLOC        |

## General Specifications

|                         |  |
|-------------------------|--|
| <b>Flexibility</b>      | Superflexible                                    |
| <b>Jacket Color</b>     | Black  |
| <b>Performance Note</b> | Attenuation values typical, guaranteed within 5% |

## Dimensions

|                                 |                     |
|---------------------------------|---------------------|
| <b>Diameter Over Dielectric</b> | 4.826 mm   0.19 in  |
| <b>Diameter Over Jacket</b>     | 7.62 mm   0.3 in    |
| <b>Inner Conductor OD</b>       | 1.905 mm   0.075 in |
| <b>Outer Conductor OD</b>       | 6.35 mm   0.25 in   |
| <b>Nominal Size</b>             | 1/4 in              |

## Electrical Specifications

|  |                                |
|--|--------------------------------|
| <b>Cable Impedance</b>                 | 50 ohm ±1 ohm                  |
| <b>Capacitance</b>                     | 79.4 pF/m   24.201 pF/ft       |
| <b>dc Resistance, Inner Conductor</b>  | 9.843 ohms/km   3 ohms/kft     |
| <b>dc Resistance, Outer Conductor</b>  | 7.216 ohms/km   2.199 ohms/kft |
| <b>dc Test Voltage</b>                 | 1600 V                         |
| <b>Inductance</b>                      | 0.2 µH/m   0.061 µH/ft         |
| <b>Insulation Resistance</b>           | 100000 MOhms-km                |
| <b>Jacket Spark Test Voltage (rms)</b> | 4000 V                         |
| <b>Operating Frequency Band</b>        | 1 – 18000 MHz                  |
| <b>Peak Power</b>                      | 6.4 kW                         |
| <b>Velocity</b>                        | 82 %                           |

# FSJ1RK-50A

---

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 680–960 MHz    | 1.201 | 20.79            |
| 1700–2200 MHz  | 1.201 | 20.79            |
| 2200–2700 MHz  | 1.433 | 14.99            |

## Attenuation

| Frequency (MHz) | Attenuation (dB/100 m) | Attenuation (dB/100 ft) | Average Power (kW) |
|-----------------|------------------------|-------------------------|--------------------|
| 1.0             | 0.577                  | 0.176                   | 6.4                |
| 1.5             | 0.707                  | 0.215                   | 6.4                |
| 2.0             | 0.816                  | 0.249                   | 6.4                |
| 10.0            | 1.833                  | 0.559                   | 3.99               |
| 20.0            | 2.6                    | 0.792                   | 2.81               |
| 30.0            | 3.192                  | 0.973                   | 2.29               |
| 50.0            | 4.136                  | 1.261                   | 1.77               |
| 85.0            | 5.419                  | 1.652                   | 1.35               |
| 88.0            | 5.516                  | 1.681                   | 1.33               |
| 100.0           | 5.889                  | 1.795                   | 1.24               |
| 108.0           | 6.125                  | 1.867                   | 1.19               |
| 150.0           | 7.25                   | 2.21                    | 1.01               |
| 174.0           | 7.825                  | 2.385                   | 0.93               |
| 200.0           | 8.408                  | 2.563                   | 0.87               |
| 204.0           | 8.495                  | 2.589                   | 0.86               |
| 300.0           | 10.373                 | 3.162                   | 0.71               |
| 400.0           | 12.051                 | 3.673                   | 0.61               |
| 450.0           | 12.817                 | 3.906                   | 0.57               |
| 460.0           | 12.965                 | 3.952                   | 0.56               |
| 500.0           | 13.545                 | 4.128                   | 0.54               |
| 512.0           | 13.715                 | 4.18                    | 0.53               |
| 600.0           | 14.909                 | 4.544                   | 0.49               |
| 700.0           | 16.175                 | 4.93                    | 0.45               |
| 800.0           | 17.362                 | 5.292                   | 0.42               |
| 824.0           | 17.637                 | 5.376                   | 0.41               |

# FSJ1RK-50A

---

|               |        |        |      |
|---------------|--------|--------|------|
| <b>894.0</b>  | 18.42  | 5.614  | 0.4  |
| <b>960.0</b>  | 19.134 | 5.832  | 0.38 |
| <b>1000.0</b> | 19.556 | 5.96   | 0.37 |
| <b>1218.0</b> | 21.738 | 6.626  | 0.34 |
| <b>1250.0</b> | 22.044 | 6.719  | 0.33 |
| <b>1500.0</b> | 24.326 | 7.414  | 0.3  |
| <b>1700.0</b> | 26.038 | 7.936  | 0.28 |
| <b>1794.0</b> | 26.813 | 8.172  | 0.27 |
| <b>1800.0</b> | 26.862 | 8.187  | 0.27 |
| <b>2000.0</b> | 28.455 | 8.673  | 0.26 |
| <b>2100.0</b> | 29.227 | 8.908  | 0.25 |
| <b>2200.0</b> | 29.984 | 9.139  | 0.24 |
| <b>2300.0</b> | 30.727 | 9.365  | 0.24 |
| <b>2500.0</b> | 32.174 | 9.806  | 0.23 |
| <b>2700.0</b> | 33.576 | 10.233 | 0.22 |
| <b>3000.0</b> | 35.602 | 10.851 | 0.21 |
| <b>3400.0</b> | 38.183 | 11.638 | 0.19 |
| <b>3600.0</b> | 39.428 | 12.017 | 0.19 |
| <b>3700.0</b> | 40.041 | 12.204 | 0.18 |
| <b>3800.0</b> | 40.647 | 12.389 | 0.18 |
| <b>3900.0</b> | 41.247 | 12.571 | 0.18 |
| <b>4000.0</b> | 41.841 | 12.753 | 0.17 |
| <b>4100.0</b> | 42.429 | 12.932 | 0.17 |
| <b>4200.0</b> | 43.012 | 13.11  | 0.17 |
| <b>4300.0</b> | 43.59  | 13.286 | 0.17 |
| <b>4400.0</b> | 44.163 | 13.46  | 0.17 |
| <b>4500.0</b> | 44.73  | 13.633 | 0.16 |
| <b>4600.0</b> | 45.293 | 13.805 | 0.16 |
| <b>4700.0</b> | 45.852 | 13.975 | 0.16 |
| <b>4800.0</b> | 46.405 | 14.144 | 0.16 |
| <b>4900.0</b> | 46.955 | 14.311 | 0.16 |
| <b>5000.0</b> | 47.5   | 14.477 | 0.15 |
| <b>6000.0</b> | 52.747 | 16.077 | 0.14 |
| <b>8000.0</b> | 62.37  | 19.01  | 0.12 |
| <b>8800.0</b> | 65.974 | 20.108 | 0.11 |

# FSJ1RK-50A

|                |         |        |      |
|----------------|---------|--------|------|
| <b>10000.0</b> | 71.173  | 21.693 | 0.1  |
| <b>12000.0</b> | 79.393  | 24.198 | 0.09 |
| <b>14000.0</b> | 87.172  | 26.569 | 0.08 |
| <b>15800.0</b> | 93.872  | 28.611 | 0.08 |
| <b>16000.0</b> | 94.601  | 28.833 | 0.08 |
| <b>18000.0</b> | 101.745 | 31.01  | 0.07 |

## Material Specifications

|                                 |  |
|---------------------------------|--|
| <b>Dielectric Material</b>      | Foam PE                                    |
| <b>Jacket Material</b>          | Non-halogenated, fire retardant polyolefin |
| <b>Inner Conductor Material</b> | Copper-clad aluminum wire                  |
| <b>Outer Conductor Material</b> | Corrugated copper                          |

## Mechanical Specifications

|  |                           |
|--|---------------------------|
| <b>Minimum Bend Radius, multiple Bends</b> | 25.4 mm   1 in            |
| <b>Minimum Bend Radius, single Bend</b>    | 25.4 mm   1 in            |
| <b>Number of Bends, minimum</b>            | 15                        |
| <b>Number of Bends, typical</b>            | 20                        |
| <b>Tensile Strength</b>                    | 68 kg   149.914 lb        |
| <b>Bending Moment</b>                      | 0.7 N-m   6.196 in lb     |
| <b>Flat Plate Crush Strength</b>           | 1.8 kg/mm   100.795 lb/in |

## Environmental Specifications

|   |                                      |
|---|--------------------------------------|
| <b>Installation temperature</b>                     | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Operating Temperature</b>                        | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Storage Temperature</b>                          | -40 °C to +60 °C (-40 °F to +140 °F) |
| <b>Attenuation, Ambient Temperature</b>             | 68 °F   20 °C                        |
| <b>Average Power, Ambient Temperature</b>           | 104 °F   40 °C                       |
| <b>Average Power, Inner Conductor Temperature</b>   | 212 °F   100 °C                      |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca                                 |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a                                  |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d0                                   |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1                                   |

# FSJ1RK-50A

---

**Fire Retardancy Test Method**

IEC 60332-1-2 | IEC 60332-3-24 | NFPA 130-2010 | UL 1666/CATVR /CMR | UL 1685

**Smoke Index Test Method**

IEC 61034

**Toxicity Index Test Method**

IEC 60754-1 | IEC 60754-2

## Packaging and Weights

**Cable weight**

0.07 kg/m | 0.047 lb/ft

## Regulatory Compliance/Certifications

**Agency**

**Classification**

|                      |  |
|----------------------|--|
| CENELEC              | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS           | Below maximum concentration value  |
| ISO 9001:2015        | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC           | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS                 | Compliant  |
| UK-ROHS              | Compliant  |
| UL/ETL Certification | Compliant  |

